

Garant
Left-hand thread through hole machine tap, TiN, MF: M34X3

Order data

| | |
|--------------|---------------|
| Order number | 130006 M34X3 |
| GTIN | 4062406009847 |
| Item class | 10N |

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 3 mm

Overall length L: 200 mm

Shank \varnothing D_s: 28 mm

Shank square □: 22 mm

Tapping hole \varnothing : 31 mm

Technical description

| | |
|--------------------------|----------|
| Standard | DIN 376 |
| Tool material | HSS E |
| Thread \varnothing | 34 mm |
| Number of clamping slots | 4 |
| Overall length L | 200 mm |
| Tolerance class | ISO 1 4H |

| | |
|----------------------------------|--|
| Tolerance class | ISO 1X 4HX |
| Tolerance class | ISO 2 6H |
| Tolerance class | ISO 2X 6HX |
| Tolerance class | 6H +0.05 |
| Tolerance class | 6H +0.20 |
| Tolerance class | ISO 3 6G |
| Tolerance class | ISO 3X 6GX |
| Tolerance class | 7H |
| Tolerance class | 7HX |
| Tolerance class | 7G |
| Tolerance class | 7GX |
| Tolerance class | 6H +0.10 |
| Number of cutting edges Z | 4 |
| Thread depth | 102 mm |
| Shank $\varnothing D_s$ | 28 mm |
| Shank square \square | 22 mm |
| Tapping hole \varnothing | 31 mm |
| Thread pitch | 3 mm |
| Thread type | MF-LH |
| Thread size | M34x3 |
| Coating | TiN |
| Flank angle | 60° |
| Thread standard | DIN 13 |
| Taper lead form | B |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 3xD for through holes |
| Cutting direction | left-hand |
| Type of threading tool | Machine tap for conventional machining |

| | |
|-----------------|---------|
| Colour ring | without |
| Type of product | Tap |