

Garant**Left-hand thread blind hole machine tap, uncoated, MF: M2,5X0,25****Order data**

| | |
|--------------|------------------|
| Order number | 130011 M2,5X0,25 |
| GTIN | 4062406014759 |
| Item class | 10N |

Description**Note:**

Delivery time: 91 calendar days

Minimum order quantity: 25 pcs.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.25 mm

Overall length L: 50 mm

Shank \varnothing D_s: 2.8 mmShank square \square : 2.1 mmTapping hole \varnothing : 2.25 mm**Technical description**

| | |
|---------------------------|---------|
| Number of clamping slots | 3 |
| Tool material | HSS E |
| Number of cutting edges Z | 3 |
| Shank square \square | 2.1 mm |
| Thread pitch | 0.25 mm |
| Overall length L | 50 mm |

| | |
|----------------------------------|--|
| Tolerance class | ISO 1 4H |
| Tolerance class | ISO 1X 4HX |
| Tolerance class | ISO 2 6H |
| Tolerance class | ISO 2X 6HX |
| Tolerance class | 6H +0.05 |
| Tolerance class | 6H +0.20 |
| Tolerance class | ISO 3 6G |
| Tolerance class | ISO 3X 6GX |
| Tolerance class | 7H |
| Tolerance class | 7HX |
| Tolerance class | 7G |
| Tolerance class | 7GX |
| Tolerance class | 6H +0.10 |
| Tapping hole Ø | 2.25 mm |
| Shank Ø D _s | 2.8 mm |
| Thread depth | 6.25 mm |
| Standard | DIN 371 |
| Thread Ø | 2.5 mm |
| Thread type | MF-LH |
| Thread size | M2.5×0.25 |
| Coating | uncoated |
| Flank angle | 60° |
| Thread standard | DIN 13 |
| Taper lead form | C |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 2×D for blind holes |
| Cutting direction | left-hand |
| Type of threading tool | Machine tap for conventional machining |

| | |
|-----------------|---------|
| Colour ring | without |
| Type of product | Tap |