

**Garant**
**Left-hand thread through hole machine tap, TiN, MF: M36X3**

**Order data**

Order number	130006 M36X3
GTIN	4062406010003
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: MF-LH  
 Tool material: HSS E  
 Standard: DIN 376  
 Tolerance class: ISO 1 4H  
 Tolerance class: ISO 1X 4HX  
 Tolerance class: ISO 2 6H  
 Thread pitch: 3 mm  
 Overall length L: 200 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 28 mm  
 Shank square □: 22 mm  
 Tapping hole  $\varnothing$ : 33 mm

**Technical description**

Tool material	HSS E
Shank square □	22 mm
Thread depth	108 mm
Thread pitch	3 mm
Tapping hole $\varnothing$	33 mm
Thread $\varnothing$	36 mm

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Number of clamping slots	4
Number of cutting edges Z	4
Standard	DIN 376
Shank $\varnothing D_s$	28 mm
Overall length L	200 mm
Thread type	MF-LH
Thread size	M36×3
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap