

Garant
Left-hand thread blind hole machine tap, uncoated, MF: M2X0,35

Order data

| | |
|--------------|----------------|
| Order number | 130011 M2X0,35 |
| GTIN | 4062406014681 |
| Item class | 10N |

Description
Note:

Delivery time: 91 calendar days
 Minimum order quantity: 25 pcs.
 Special / custom-made product - return not possible
 Thread type: MF-LH
 Tool material: HSS E
 Standard: DIN 371
 Tolerance class: ISO 1 4H
 Tolerance class: ISO 1X 4HX
 Tolerance class: ISO 2 6H
 Thread pitch: 0.35 mm
 Overall length L: 45 mm
 Shank $\varnothing D_s$: 2.8 mm
 Shank square \square : 2.1 mm
 Tapping hole \varnothing : 1.65 mm

Technical description

| | |
|-------------------------|---------|
| Thread \varnothing | 2 mm |
| Thread pitch | 0.35 mm |
| Shank $\varnothing D_s$ | 2.8 mm |
| Overall length L | 45 mm |
| Shank square \square | 2.1 mm |
| Thread depth | 5 mm |

| | |
|----------------------------------|--|
| Number of clamping slots | 3 |
| Tolerance class | ISO 1 4H |
| Tolerance class | ISO 1X 4HX |
| Tolerance class | ISO 2 6H |
| Tolerance class | ISO 2X 6HX |
| Tolerance class | 6H +0.05 |
| Tolerance class | 6H +0.20 |
| Tolerance class | ISO 3 6G |
| Tolerance class | ISO 3X 6GX |
| Tolerance class | 7H |
| Tolerance class | 7HX |
| Tolerance class | 7G |
| Tolerance class | 7GX |
| Tolerance class | 6H +0.10 |
| Tapping hole Ø | 1.65 mm |
| Tool material | HSS E |
| Number of cutting edges Z | 3 |
| Standard | DIN 371 |
| Thread type | MF-LH |
| Thread size | M2×0.35 |
| Coating | uncoated |
| Flank angle | 60° |
| Thread standard | DIN 13 |
| Taper lead form | C |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 2×D for blind holes |
| Cutting direction | left-hand |
| Type of threading tool | Machine tap for conventional machining |

| | |
|-----------------|---------|
| Colour ring | without |
| Type of product | Tap |