

Garant**Left-hand thread blind hole machine tap, uncoated, MF: M20X2,5****Order data**

Order number	130011 M20X2,5
GTIN	4062406015947
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: M-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 2.5 mm

Overall length L: 140 mm

Shank $\varnothing D_s$: 16 mmShank square \square : 12 mmTapping hole \varnothing : 17.5 mm**Technical description**

Tool material	HSS E
Overall length L	140 mm
Shank $\varnothing D_s$	16 mm
Standard	DIN 376
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX

Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tapping hole Ø	17.5 mm
Shank square □	12 mm
Number of clamping slots	3
Thread pitch	2.5 mm
Number of cutting edges Z	3
Thread depth	50 mm
Thread Ø	20 mm
Thread type	M-LH
Thread size	M20×2.5
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap