

Garant
Spiral flute machine tap, uncoated, MF: M2,5X0,45

Order data

Order number	130010 M2,5X0,45
GTIN	4062406011178
Item class	10N

Description
Note:

Delivery time: 91 calendar days

Minimum order quantity: 25 pcs.

Special / custom-made product - return not possible

Technical description

Thread pitch	0.45 mm
Thread Ø	2.5 mm
Standard	DIN 371
Shank Ø D _s	2.8 mm
Number of cutting edges Z	3
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX

Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Number of clamping slots	3
Shank square □	2.1 mm
Overall length L	50 mm
Thread depth	6.25 mm
Tapping hole Ø	2.05 mm
Tool material	HSS E
Thread type	M
Thread size	M2.5×0.45
Coating	uncoated
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap