

Garant
Spiral flute machine tap, uncoated, MF: M39X2

Order data

Order number	130010 M39X2
GTIN	4062406013813
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: M
 Tool material: HSS E
 Standard: DIN 376
 Tolerance class: ISO 1 4H
 Tolerance class: ISO 1X 4HX
 Tolerance class: ISO 2 6H
 Thread pitch: 2 mm
 Overall length L: 200 mm
 Shank \varnothing D_s: 32 mm
 Shank square □: 24 mm
 Tapping hole \varnothing : 37 mm

Technical description

Overall length L	200 mm
Thread pitch	2 mm
Thread \varnothing	39 mm
Number of clamping slots	4
Number of cutting edges Z	4
Tolerance class	ISO 1 4H

Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Shank square □	24 mm
Tapping hole Ø	37 mm
Shank Ø D _s	32 mm
Tool material	HSS E
Thread depth	97.5 mm
Standard	DIN 376
Thread type	M
Thread size	M39×2
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap