

**Garant****Left-hand thread blind hole machine tap, uncoated, MF: M35X1****Order data**

Order number	130011 M35X1
GTIN	4062406017088
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 1 mm

Overall length L: 200 mm

Shank  $\varnothing$  D<sub>s</sub>: 28 mm

Shank square □: 22 mm

Tapping hole  $\varnothing$ : 34 mm**Technical description**

Number of cutting edges Z	4
Thread depth	87.5 mm
Number of clamping slots	4
Thread $\varnothing$	35 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX

Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Overall length L	200 mm
Shank square □	22 mm
Standard	DIN 376
Tool material	HSS E
Thread pitch	1 mm
Shank $\varnothing D_s$	28 mm
Tapping hole $\varnothing$	34 mm
Thread type	MF-LH
Thread size	M35×1
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap