

Garant
Left-hand thread blind hole machine tap, uncoated, MF: M23X2

Order data

Order number	130011 M23X2
GTIN	4062406016166
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: MF-LH
 Tool material: HSS E
 Standard: DIN 376
 Tolerance class: ISO 1 4H
 Tolerance class: ISO 1X 4HX
 Tolerance class: ISO 2 6H
 Thread pitch: 2 mm
 Overall length L: 160 mm
 Shank $\varnothing D_s$: 18 mm
 Shank square \square : 14.5 mm
 Tapping hole \varnothing : 21 mm

Technical description

Shank square \square	14.5 mm
Overall length L	160 mm
Thread depth	57.5 mm
Shank $\varnothing D_s$	18 mm
Tapping hole \varnothing	21 mm
Number of clamping slots	3

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread pitch	2 mm
Standard	DIN 376
Number of cutting edges Z	3
Thread Ø	23 mm
Tool material	HSS E
Thread type	MF-LH
Thread size	M23×2
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap