

Garant
Left-hand thread blind hole machine tap, uncoated, MF: M43X0,5

Order data

Order number	130011 M43X0,5
GTIN	4062406017644
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 220 mm

Shank \varnothing D_s: 36 mm

Shank square □: 29 mm

Tapping hole \varnothing : 42.5 mm

Technical description

Number of cutting edges Z	4
Shank square □	29 mm
Overall length L	220 mm
Standard	DIN 376
Tool material	HSS E
Tapping hole \varnothing	42.5 mm

Thread depth	107.5 mm
Thread pitch	0.5 mm
Shank $\varnothing D_s$	36 mm
Number of clamping slots	4
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread \varnothing	43 mm
Thread type	MF-LH
Thread size	M43×0.5
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap