

Garant
Left-hand thread blind hole machine tap, TiN, MF: M30X0,5

Order data

Order number	130016 M30X0,5
GTIN	4062406023850
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 180 mm

Shank \varnothing D_s: 22 mm

Shank square □: 18 mm

Tapping hole \varnothing : 29.5 mm

Technical description

Tool material	HSS E
Overall length L	180 mm
Thread pitch	0.5 mm
Shank square □	18 mm
Number of cutting edges Z	4
Thread \varnothing	30 mm

Thread depth	75 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tapping hole Ø	29.5 mm
Shank Ø D _s	22 mm
Number of clamping slots	4
Standard	DIN 376
Thread type	MF-LH
Thread size	M30×0.5 LH
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap