

Garant
Spiral flute machine tap, uncoated, MF: M28X0,35

Order data

Order number	130010 M28X0,35
GTIN	4062406012915
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Technical description

Shank $\varnothing D_s$	20 mm
Number of cutting edges Z	4
Shank square \square	16 mm
Number of clamping slots	4
Tapping hole \varnothing	27.65 mm
Standard	DIN 376
Tool material	HSS E
Thread depth	70 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05

Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread Ø	28 mm
Overall length L	140 mm
Thread pitch	0.35 mm
Thread type	M
Thread size	M28×0.35
Coating	uncoated
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap