

Garant
Left-hand thread blind hole machine tap, uncoated, MF: M30X2

Order data

Order number	130011 M30X2
GTIN	4062406016722
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: MF-LH
 Tool material: HSS E
 Standard: DIN 376
 Tolerance class: ISO 1 4H
 Tolerance class: ISO 1X 4HX
 Tolerance class: ISO 2 6H
 Thread pitch: 2 mm
 Overall length L: 180 mm
 Shank \varnothing D_s: 22 mm
 Shank square □: 18 mm
 Tapping hole \varnothing : 28 mm

Technical description

Number of clamping slots	3
Standard	DIN 376
Number of cutting edges Z	3
Tapping hole \varnothing	28 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX

Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Overall length L	180 mm
Shank $\varnothing D_s$	22 mm
Thread pitch	2 mm
Tool material	HSS E
Shank square \square	18 mm
Thread \varnothing	30 mm
Thread depth	75 mm
Thread type	MF-LH
Thread size	M30x2
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap