

Garant**Left-hand thread blind hole machine tap, TiN, MF: M27X2****Order data**

Order number	130016 M27X2
GTIN	4062406023683
Item class	10N

Description**Note:**

Delivery time: 49 calendar days
Minimum order quantity: 1 pc.
Special / custom-made product - return not possible
Thread type: MF-LH
Tool material: HSS E
Standard: DIN 376
Tolerance class: ISO 1 4H
Tolerance class: ISO 1X 4HX
Tolerance class: ISO 2 6H
Thread pitch: 2 mm
Overall length L: 160 mm
Shank $\varnothing D_s$: 20 mm
Shank square \square : 16 mm
Tapping hole \varnothing : 25 mm

Technical description

Thread depth	67.5 mm
Thread pitch	2 mm
Number of clamping slots	4
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H

Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tool material	HSS E
Shank $\varnothing D_s$	20 mm
Thread \varnothing	27 mm
Tapping hole \varnothing	25 mm
Shank square \square	16 mm
Standard	DIN 376
Number of cutting edges Z	4
Overall length L	160 mm
Thread type	MF-LH
Thread size	M27x2
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap