

**Garant**
**Left-hand thread blind hole machine tap, TiN, MF: M34X1**

**Order data**

Order number	130016 M34X1
GTIN	4062406024185
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: MF-LH  
 Tool material: HSS E  
 Standard: DIN 376  
 Tolerance class: ISO 1 4H  
 Tolerance class: ISO 1X 4HX  
 Tolerance class: ISO 2 6H  
 Thread pitch: 1 mm  
 Overall length L: 200 mm  
 Shank  $\varnothing D_s$ : 28 mm  
 Shank square  $\square$ : 22 mm  
 Tapping hole  $\varnothing$ : 33 mm

**Technical description**

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20

Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tool material	HSS E
Number of cutting edges Z	4
Tapping hole Ø	33 mm
Standard	DIN 376
Overall length L	200 mm
Thread pitch	1 mm
Number of clamping slots	4
Shank Ø D <sub>s</sub>	28 mm
Shank square □	22 mm
Thread Ø	34 mm
Thread depth	85 mm
Thread type	MF-LH
Thread size	M34×1
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap