

Garant
Left-hand thread blind hole machine tap, uncoated, MF: M38X1,75

Order data

Order number	130011 M38X1,75
GTIN	4062406017330
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 1.75 mm

Overall length L: 200 mm

Shank \varnothing D_s: 32 mm

Shank square \square : 24 mm

Tapping hole \varnothing : 36.25 mm

Technical description

Thread pitch	1.75 mm
Number of cutting edges Z	4
Shank square \square	24 mm
Thread depth	95 mm
Standard	DIN 376
Thread \varnothing	38 mm

Number of clamping slots	4
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Shank $\varnothing D_s$	32 mm
Tool material	HSS E
Overall length L	200 mm
Tapping hole \varnothing	36.25 mm
Thread type	MF-LH
Thread size	M38x1.75
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap