

Garant
Left-hand thread blind hole machine tap, TiN, MF: M29X0,35

Order data

Order number	130016 M29X0,35
GTIN	4062406023799
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.35 mm

Overall length L: 180 mm

Shank \varnothing D_s: 22 mm

Shank square □: 18 mm

Tapping hole \varnothing : 28.65 mm

Technical description

Shank square □	18 mm
Overall length L	180 mm
Number of cutting edges Z	4
Standard	DIN 376
Tapping hole \varnothing	28.65 mm
Thread \varnothing	29 mm

Thread pitch	0.35 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tool material	HSS E
Thread depth	72.5 mm
Shank $\varnothing D_s$	22 mm
Number of clamping slots	4
Thread type	MF-LH
Thread size	M29×0.35
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap