

**Garant**
**Left-hand thread blind hole machine tap, uncoated, MF: M27X3**

**Order data**

Order number	130011 M27X3
GTIN	4062406016500
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: M-LH  
 Tool material: HSS E  
 Standard: DIN 376  
 Tolerance class: ISO 1 4H  
 Tolerance class: ISO 1X 4HX  
 Tolerance class: ISO 2 6H  
 Thread pitch: 3 mm  
 Overall length L: 160 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 20 mm  
 Shank square □: 16 mm  
 Tapping hole  $\varnothing$ : 24 mm

**Technical description**

Thread depth	67.5 mm
Number of clamping slots	3
Number of cutting edges Z	3
Tool material	HSS E
Tapping hole $\varnothing$	24 mm
Standard	DIN 376

Overall length L	160 mm
Shank square □	16 mm
Thread Ø	27 mm
Thread pitch	3 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Shank Ø D <sub>s</sub>	20 mm
Thread type	M-LH
Thread size	M27×3
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap