

Garant
Left-hand thread blind hole machine tap, uncoated, MF: M37X0,75

Order data

Order number	130011 M37X0,75
GTIN	4062406017248
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.75 mm

Overall length L: 200 mm

Shank $\varnothing D_s$: 32 mm

Shank square \square : 24 mm

Tapping hole \varnothing : 36.25 mm

Technical description

Standard	DIN 376
Thread \varnothing	37 mm
Number of cutting edges Z	4
Thread pitch	0.75 mm
Shank $\varnothing D_s$	32 mm
Tapping hole \varnothing	36.25 mm

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Shank square □	24 mm
Thread depth	92.5 mm
Number of clamping slots	4
Overall length L	200 mm
Tool material	HSS E
Thread type	MF-LH
Thread size	M37×0.75
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap