

Garant
Machine tap for through holes and blind holes, uncoated, MF: M56X5,5

Order data

Order number	130020 M56X5,5
GTIN	4062406025489
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS

Standard: DIN 2184

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 5.5 mm

Overall length L: 140 mm

Shank $\varnothing D_s$: 40 mm

Shank square \square : 32 mm

Tapping hole \varnothing : 50.5 mm

Technical description

Tool material	HSS
Number of clamping slots	6
Tapping hole \varnothing	50.5 mm
Standard	DIN 2184
Thread \varnothing	56 mm
Overall length L	140 mm

Thread depth	84 mm
Thread pitch	5.5 mm
Shank square □	32 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Shank $\varnothing D_s$	40 mm
Number of cutting edges Z	6
Thread type	M
Thread size	M56×5.5
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Application for type of drilling	up to 1.5×D for blind holes
Cutting direction	right-hand

Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap