

Garant**Left-hand thread blind hole machine tap, uncoated, MF: M18X2****Order data**

Order number	130011 M18X2
GTIN	4062406015763
Item class	10N

Description**Note:**

Delivery time: 35 calendar days
Minimum order quantity: 2 pcs.
Special / custom-made product - return not possible
Thread type: MF-LH
Tool material: HSS E
Standard: DIN 376
Tolerance class: ISO 1 4H
Tolerance class: ISO 1X 4HX
Tolerance class: ISO 2 6H
Thread pitch: 2 mm
Overall length L: 125 mm
Shank $\varnothing D_s$: 14 mm
Shank square \square : 11 mm
Tapping hole \varnothing : 16 mm

Technical description

Shank $\varnothing D_s$	14 mm
Standard	DIN 376
Tapping hole \varnothing	16 mm
Thread depth	45 mm
Thread \varnothing	18 mm
Thread pitch	2 mm

Tool material	HSS E
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Shank square <input type="checkbox"/>	11 mm
Number of cutting edges Z	3
Overall length L	125 mm
Number of clamping slots	3
Thread type	MF-LH
Thread size	M18×2
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap