

**Garant**
**Spiral flute machine tap, uncoated, MF: M35X0,75**

**Order data**

Order number	130010 M35X0,75
GTIN	4062406013479
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

**Technical description**

Shank square <input type="checkbox"/>	22 mm
Thread pitch	0.75 mm
Overall length L	200 mm
Thread depth	87.5 mm
Tapping hole Ø	34.25 mm
Number of clamping slots	4
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G

Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Shank $\varnothing D_s$	28 mm
Standard	DIN 376
Number of cutting edges Z	4
Thread $\varnothing$	35 mm
Tool material	HSS E
Thread type	M
Thread size	M35x0.75
Coating	uncoated
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap