

Garant
Left-hand thread blind hole machine tap, uncoated, MF: M10X1,5

Order data

Order number	130011 M10X1,5
GTIN	4062406015176
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: M-LH

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 1.5 mm

Overall length L: 100 mm

Shank \varnothing D_s: 10 mm

Shank square □: 8 mm

Tapping hole \varnothing : 8.5 mm

Technical description

Overall length L	100 mm
Number of cutting edges Z	2
Tool material	HSS E
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H

Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Standard	DIN 371
Thread Ø	10 mm
Shank square □	8 mm
Thread pitch	1.5 mm
Thread depth	25 mm
Number of clamping slots	2
Tapping hole Ø	8.5 mm
Shank Ø D _s	10 mm
Thread type	M-LH
Thread size	M10×1.5
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap