

**Garant****Left-hand thread blind hole machine tap, uncoated, MF: M17X1,75****Order data**

Order number	130011 M17X1,75
GTIN	4062406015671
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days  
Minimum order quantity: 2 pcs.  
Special / custom-made product - return not possible  
Thread type: MF-LH  
Tool material: HSS E  
Standard: DIN 376  
Tolerance class: ISO 1 4H  
Tolerance class: ISO 1X 4HX  
Tolerance class: ISO 2 6H  
Thread pitch: 1.75 mm  
Overall length L: 125 mm  
Shank  $\varnothing$  D<sub>s</sub>: 14 mm  
Shank square  $\square$ : 11 mm  
Tapping hole  $\varnothing$ : 15.25 mm

**Technical description**

Shank square $\square$	11 mm
Thread pitch	1.75 mm
Overall length L	125 mm
Thread $\varnothing$	17 mm
Standard	DIN 376
Tool material	HSS E

Shank $\varnothing D_s$	14 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Number of clamping slots	3
Tapping hole $\varnothing$	15.25 mm
Number of cutting edges Z	3
Thread depth	42.5 mm
Thread type	MF-LH
Thread size	M17×1.75
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap