

Garant
Left-hand thread blind hole machine tap, uncoated, MF: M7X0,5

Order data

Order number	130011 M7X0,5
GTIN	4062406014995
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 3 pcs.
 Special / custom-made product - return not possible
 Thread type: MF-LH
 Tool material: HSS E
 Standard: DIN 371
 Tolerance class: ISO 1 4H
 Tolerance class: ISO 1X 4HX
 Tolerance class: ISO 2 6H
 Thread pitch: 0.5 mm
 Overall length L: 80 mm
 Shank $\varnothing D_s$: 7 mm
 Shank square \square : 5.5 mm
 Tapping hole \varnothing : 6.5 mm

Technical description

Thread depth	17.5 mm
Thread \varnothing	7 mm
Tool material	HSS E
Number of clamping slots	3
Shank square \square	5.5 mm
Number of cutting edges Z	3

Tapping hole Ø	6.5 mm
Standard	DIN 371
Thread pitch	0.5 mm
Shank Ø D _s	7 mm
Overall length L	80 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread type	MF-LH
Thread size	M7×0.5
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap