

**Garant****Left-hand thread blind hole machine tap, uncoated, MF: M3,5X0,5****Order data**

Order number	130011 M3,5X0,5
GTIN	4062406014810
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days  
Minimum order quantity: 3 pcs.  
Special / custom-made product - return not possible  
Thread type: MF-LH  
Tool material: HSS E  
Standard: DIN 371  
Tolerance class: ISO 1 4H  
Tolerance class: ISO 1X 4HX  
Tolerance class: ISO 2 6H  
Thread pitch: 0.5 mm  
Overall length L: 56 mm  
Shank  $\varnothing D_s$ : 4 mm  
Shank square  $\square$ : 3 mm  
Tapping hole  $\varnothing$ : 3 mm

**Technical description**

Thread depth	8.75 mm
Standard	DIN 371
Number of cutting edges Z	3
Shank square $\square$	3 mm
Thread $\varnothing$	3.5 mm
Tolerance class	ISO 1 4H

Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Overall length L	56 mm
Tool material	HSS E
Thread pitch	0.5 mm
Number of clamping slots	3
Tapping hole Ø	3 mm
Shank Ø D <sub>s</sub>	4 mm
Thread type	MF-LH
Thread size	M3.5×0.5
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap