

**Garant**
**Machine tap for through holes and blind holes, uncoated, MF: M60X0,75**

**Order data**

Order number	130020 M60X0,75
GTIN	4062406025618
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS

Standard: DIN 2184

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.75 mm

Overall length L: 160 mm

Shank  $\varnothing D_s$ : 45 mm

Shank square  $\square$ : 35 mm

Tapping hole  $\varnothing$ : 59.25 mm

**Technical description**

Thread depth	90 mm
Standard	DIN 2184
Shank square $\square$	35 mm
Number of clamping slots	6
Tapping hole $\varnothing$	59.25 mm
Thread pitch	0.75 mm

Thread Ø	60 mm
Overall length L	160 mm
Number of cutting edges Z	6
Shank Ø D <sub>s</sub>	45 mm
Tool material	HSS
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread type	M
Thread size	M60×0.75
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Application for type of drilling	up to 1.5×D for blind holes
Cutting direction	right-hand

Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap