

Garant
Spiral flute machine tap, uncoated, MF: M8X1,25

Order data

Order number	130010 M8X1,25
GTIN	4062406011468
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Technical description

Thread \varnothing	8 mm
Thread pitch	1.25 mm
Tapping hole \varnothing	6.75 mm
Tool material	HSS E
Number of clamping slots	3
Shank $\varnothing D_s$	8 mm
Shank square \square	6.2 mm
Thread depth	20 mm
Overall length L	90 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX

Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Number of cutting edges Z	3
Standard	DIN 371
Thread type	M
Thread size	M8×1.25
Coating	uncoated
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap