

Garant**Left-hand thread blind hole machine tap, uncoated, MF: M17X0,5****Order data**

Order number	130011 M17X0,5
GTIN	4062406015626
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 125 mm

Shank \varnothing D_s: 14 mmShank square \square : 11 mmTapping hole \varnothing : 16.5 mm**Technical description**

Number of cutting edges Z	3
Thread depth	42.5 mm
Number of clamping slots	3
Thread pitch	0.5 mm
Thread \varnothing	17 mm
Tolerance class	ISO 1 4H

Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Shank $\varnothing D_s$	14 mm
Standard	DIN 376
Tool material	HSS E
Shank square \square	11 mm
Overall length L	125 mm
Tapping hole \varnothing	16.5 mm
Thread type	MF-LH
Thread size	M17×0.5
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap