

**Garant**
**Left-hand thread through hole and blind hole machine tap, uncoated, MF: M53X0,75**

**Order data**

Order number	130021 M53X0,75
GTIN	4062406027544
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS

Standard: DIN 2184

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.75 mm

Overall length L: 140 mm

Shank  $\varnothing$  D<sub>s</sub>: 40 mm

Shank square □: 32 mm

Tapping hole  $\varnothing$ : 52.25 mm

**Technical description**

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.20

Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.05
Tolerance class	6H +0.10
Thread pitch	0.75 mm
Shank $\varnothing D_s$	40 mm
Overall length L	140 mm
Number of clamping slots	6
Tapping hole $\varnothing$	52.25 mm
Standard	DIN 2184
Thread $\varnothing$	53 mm
Thread depth	79.5 mm
Shank square $\square$	32 mm
Number of cutting edges Z	6
Tool material	HSS
Thread type	MF-LH
Thread size	M53×0.75
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Application for type of drilling	up to 1.5×D for blind holes

Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap