

**Garant****Machine tap for through holes and blind holes, uncoated, MF: M120X1****Order data**

Order number	130020 M120X1
GTIN	4062406027483
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS

Standard: DIN 2184

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 1 mm

Overall length L: 180 mm

Shank  $\varnothing D_s$ : 56 mmShank square  $\square$ : 44 mmTapping hole  $\varnothing$ : 119 mm**Technical description**

Thread depth	180 mm
Thread $\varnothing$	120 mm
Tool material	HSS
Shank square $\square$	44 mm
Overall length L	180 mm
Standard	DIN 2184

Thread pitch	1 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Shank $\varnothing D_s$	56 mm
Tapping hole $\varnothing$	119 mm
Number of clamping slots	12
Number of cutting edges Z	12
Thread type	M
Thread size	M120×1
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Application for type of drilling	up to 1.5×D for blind holes
Cutting direction	right-hand

Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap