

Garant**Left-hand thread through hole and blind hole machine tap, uncoated, MF: M110X0,75****Order data**

Order number	130021 M110X0,75
GTIN	4062406029470
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS

Standard: DIN 2184

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.75 mm

Overall length L: 180 mm

Shank \varnothing D_s: 56 mm

Shank square \square : 44 mm

Tapping hole \varnothing : 109.25 mm

Technical description

Thread pitch	0.75 mm
Number of cutting edges Z	12
Tool material	HSS
Overall length L	180 mm
Shank square \square	44 mm

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.05
Tolerance class	6H +0.10
Tapping hole Ø	109.25 mm
Thread depth	165 mm
Standard	DIN 2184
Number of clamping slots	12
Shank Ø D _s	56 mm
Thread Ø	110 mm
Thread type	MF-LH
Thread size	M110×0.75
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Application for type of drilling	up to 1.5×D for blind holes

Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap