

**Garant****Left-hand thread blind hole machine tap, uncoated, MF: M39X0,35****Order data**

Order number	130011 M39X0,35
GTIN	4062406017361
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.35 mm

Overall length L: 200 mm

Shank  $\varnothing D_s$ : 32 mm

Shank square  $\square$ : 24 mm

Tapping hole  $\varnothing$ : 38.65 mm

**Technical description**

Thread depth	97.5 mm
Thread $\varnothing$	39 mm
Shank $\varnothing D_s$	32 mm
Thread pitch	0.35 mm
Standard	DIN 376
Number of clamping slots	4

Tapping hole Ø	38.65 mm
Tool material	HSS E
Shank square □	24 mm
Overall length L	200 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Number of cutting edges Z	4
Thread type	MF-LH
Thread size	M39×0.35
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap