

Garant
Left-hand thread blind hole machine tap, TiN, MF: M20X2,5

Order data

Order number	130016 M20X2,5
GTIN	4062406023140
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: M-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 2.5 mm

Overall length L: 140 mm

Shank \varnothing D_s: 16 mm

Shank square □: 12 mm

Tapping hole \varnothing : 17.5 mm

Technical description

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20

Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Standard	DIN 376
Number of clamping slots	3
Tapping hole Ø	17.5 mm
Thread pitch	2.5 mm
Overall length L	140 mm
Shank Ø D _s	16 mm
Thread depth	50 mm
Thread Ø	20 mm
Number of cutting edges Z	3
Tool material	HSS E
Shank square □	12 mm
Thread type	M-LH
Thread size	M20×2.5
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap