

Garant
Left-hand thread through hole and blind hole machine tap, uncoated, MF: M58X0,75

Order data

Order number	130021 M58X0,75
GTIN	4062406027759
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: MF-LH
 Tool material: HSS
 Standard: DIN 2184
 Tolerance class: ISO 1 4H
 Tolerance class: ISO 1X 4HX
 Tolerance class: ISO 2 6H
 Thread pitch: 0.75 mm
 Overall length L: 160 mm
 Shank $\varnothing D_s$: 45 mm
 Shank square \square : 35 mm
 Tapping hole \varnothing : 57.25 mm

Technical description

Shank $\varnothing D_s$	45 mm
Overall length L	160 mm
Number of cutting edges Z	6
Thread \varnothing	58 mm
Thread pitch	0.75 mm

Tool material	HSS
Standard	DIN 2184
Shank square □	35 mm
Number of clamping slots	6
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.05
Tolerance class	6H +0.10
Thread depth	87 mm
Tapping hole Ø	57.25 mm
Thread type	MF-LH
Thread size	M58×0.75
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Application for type of drilling	up to 1.5×D for blind holes

Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap