

**Garant**
**Left-hand thread through hole and blind hole machine tap, uncoated, MF: M60X2**

**Order data**

Order number	130021 M60X2
GTIN	4062406027872
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS

Standard: DIN 2184

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 2 mm

Overall length L: 160 mm

Shank  $\varnothing$  D<sub>s</sub>: 45 mm

Shank square □: 35 mm

Tapping hole  $\varnothing$ : 58 mm

**Technical description**

Tapping hole $\varnothing$	58 mm
Number of clamping slots	6
Overall length L	160 mm
Thread pitch	2 mm
Tolerance class	ISO 1 4H

Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.05
Tolerance class	6H +0.10
Shank square <input type="checkbox"/>	35 mm
Standard	DIN 2184
Thread $\emptyset$	60 mm
Shank $\emptyset D_s$	45 mm
Thread depth	90 mm
Tool material	HSS
Number of cutting edges Z	6
Thread type	MF-LH
Thread size	M60x2
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5xD for through holes
Application for type of drilling	up to 1.5xD for blind holes

Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap