

Garant
Left-hand thread through hole and blind hole machine tap, uncoated, MF: M75X1

Order data

Order number	130021 M75X1
GTIN	4062406028459
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: MF-LH
 Tool material: HSS
 Standard: DIN 2184
 Tolerance class: ISO 1 4H
 Tolerance class: ISO 1X 4HX
 Tolerance class: ISO 2 6H
 Thread pitch: 1 mm
 Overall length L: 160 mm
 Shank $\varnothing D_s$: 50 mm
 Shank square \square : 39 mm
 Tapping hole \varnothing : 74 mm

Technical description

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.20

Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.05
Tolerance class	6H +0.10
Thread pitch	1 mm
Shank $\varnothing D_s$	50 mm
Overall length L	160 mm
Tapping hole \varnothing	74 mm
Standard	DIN 2184
Tool material	HSS
Number of cutting edges Z	8
Thread \varnothing	75 mm
Thread depth	112.5 mm
Shank square \square	39 mm
Number of clamping slots	8
Thread type	MF-LH
Thread size	M75×1
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Application for type of drilling	up to 1.5×D for blind holes

Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap