

Garant
Left-hand thread blind hole machine tap, uncoated, MF: M30X1,75

Order data

Order number	130011 M30X1,75
GTIN	4062406016715
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: MF-LH
 Tool material: HSS E
 Standard: DIN 376
 Tolerance class: ISO 1 4H
 Tolerance class: ISO 1X 4HX
 Tolerance class: ISO 2 6H
 Thread pitch: 1.75 mm
 Overall length L: 180 mm
 Shank $\varnothing D_s$: 22 mm
 Shank square \square : 18 mm
 Tapping hole \varnothing : 28.25 mm

Technical description

Tapping hole \varnothing	28.25 mm
Number of clamping slots	3
Shank square \square	18 mm
Tool material	HSS E
Shank $\varnothing D_s$	22 mm
Standard	DIN 376

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread pitch	1.75 mm
Thread Ø	30 mm
Number of cutting edges Z	3
Overall length L	180 mm
Thread depth	75 mm
Thread type	MF-LH
Thread size	M30×1.75
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap