

**Garant**
**Machine tap for through holes and blind holes, TiN, MF: M72X0,5**

**Order data**

|              |                |
|--------------|----------------|
| Order number | 130025 M72X0,5 |
| GTIN         | 4062406030575  |
| Item class   | 10N            |

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS

Standard: DIN 2184

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 160 mm

Shank  $\varnothing D_s$ : 50 mm

Shank square  $\square$ : 39 mm

Tapping hole  $\varnothing$ : 71.5 mm

**Technical description**

|                            |         |
|----------------------------|---------|
| Tapping hole $\varnothing$ | 71.5 mm |
| Overall length L           | 160 mm  |
| Shank $\varnothing D_s$    | 50 mm   |
| Thread $\varnothing$       | 72 mm   |
| Shank square $\square$     | 39 mm   |
| Thread pitch               | 0.5 mm  |

|                                  |                               |
|----------------------------------|-------------------------------|
| Tool material                    | HSS                           |
| Number of cutting edges Z        | 8                             |
| Number of clamping slots         | 8                             |
| Standard                         | DIN 2184                      |
| Thread depth                     | 108 mm                        |
| Tolerance class                  | ISO 1 4H                      |
| Tolerance class                  | ISO 1X 4HX                    |
| Tolerance class                  | ISO 2 6H                      |
| Tolerance class                  | ISO 2X 6HX                    |
| Tolerance class                  | 6H +0.20                      |
| Tolerance class                  | ISO 3 6G                      |
| Tolerance class                  | ISO 3X 6GX                    |
| Tolerance class                  | 7H                            |
| Tolerance class                  | 7HX                           |
| Tolerance class                  | 7G                            |
| Tolerance class                  | 7GX                           |
| Tolerance class                  | 6H +0.05                      |
| Tolerance class                  | 6H +0.10                      |
| Thread type                      | M                             |
| Thread size                      | M72×0.5                       |
| Coating                          | TiN                           |
| Flank angle                      | 60°                           |
| Thread standard                  | DIN 13                        |
| Taper lead form                  | C                             |
| Shank                            | Plain shank with h9           |
| Through-coolant                  | no                            |
| Application for type of drilling | up to 1.5×D for through holes |
| Application for type of drilling | up to 1.5×D for blind holes   |
| Cutting direction                | right-hand                    |

|                        |  |
|------------------------|--|
| Type of threading tool | Machine tap for conventional machining |
| Colour ring            | without                                |
| Type of product        | Tap                                    |