

**Garant**
**Left-hand thread through hole and blind hole machine tap, TiN, MF: M62X0,5**

**Order data**

|              |                |
|--------------|----------------|
| Order number | 130026 M62X0,5 |
| GTIN         | 4062406032371  |
| Item class   | 10N            |

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS

Standard: DIN 2184

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 160 mm

Shank  $\varnothing$  D<sub>s</sub>: 50 mm

Shank square  $\square$ : 39 mm

Tapping hole  $\varnothing$ : 61.5 mm

**Technical description**

|                            |         |
|----------------------------|---------|
| Thread depth               | 93 mm   |
| Thread pitch               | 0.5 mm  |
| Tapping hole $\varnothing$ | 61.5 mm |
| Overall length L           | 160 mm  |
| Number of clamping slots   | 6       |
| Shank square $\square$     | 39 mm   |

|                                  |                               |
|----------------------------------|-------------------------------|
| Tolerance class                  | ISO 1 4H                      |
| Tolerance class                  | ISO 1X 4HX                    |
| Tolerance class                  | ISO 2 6H                      |
| Tolerance class                  | ISO 2X 6HX                    |
| Tolerance class                  | 6H +0.20                      |
| Tolerance class                  | ISO 3 6G                      |
| Tolerance class                  | ISO 3X 6GX                    |
| Tolerance class                  | 7H                            |
| Tolerance class                  | 7HX                           |
| Tolerance class                  | 7G                            |
| Tolerance class                  | 7GX                           |
| Tolerance class                  | 6H +0.05                      |
| Tolerance class                  | 6H +0.10                      |
| Standard                         | DIN 2184                      |
| Number of cutting edges Z        | 6                             |
| Thread Ø                         | 62 mm                         |
| Shank Ø D <sub>s</sub>           | 50 mm                         |
| Tool material                    | HSS                           |
| Thread type                      | MF-LH                         |
| Thread size                      | M62×0.5                       |
| Coating                          | TiN                           |
| Flank angle                      | 60°                           |
| Thread standard                  | DIN 13                        |
| Taper lead form                  | C                             |
| Shank                            | Plain shank with h9           |
| Through-coolant                  | no                            |
| Application for type of drilling | up to 1.5×D for through holes |
| Application for type of drilling | up to 1.5×D for blind holes   |
| Cutting direction                | left-hand                     |

|                        |  |
|------------------------|--|
| Type of threading tool | Machine tap for conventional machining |
| Colour ring            | without                                |
| Type of product        | Tap                                    |