

Garant
Spiral flute machine tap, TiN, MF: M1,6X0,25

Order data

Order number	130015 M1,6X0,25
GTIN	4062406018221
Item class	10N

Description
Note:

Delivery time: 91 calendar days

Minimum order quantity: 25 pcs.

Special / custom-made product - return not possible

Technical description

Standard	DIN 371
Tool material	HSS E
Number of cutting edges Z	2
Tapping hole Ø	1.35 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H

Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Shank $\varnothing D_s$	2.5 mm
Thread \varnothing	1.6 mm
Overall length L	40 mm
Shank square \square	2.1 mm
Thread pitch	0.25 mm
Number of clamping slots	2
Thread depth	4 mm
Thread type	M
Thread size	M1.6×0.25
Coating	TiN
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap