

Garant
Spiral flute machine tap, TiN, MF: M27X1,25

Order data

Order number	130015 M27X1,25
GTIN	4062406020057
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Technical description

Tool material	HSS E
Thread pitch	1.25 mm
Number of cutting edges Z	4
Shank square <input type="checkbox"/>	16 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H

Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread Ø	27 mm
Standard	DIN 376
Shank Ø D _s	20 mm
Tapping hole Ø	25.75 mm
Number of clamping slots	4
Overall length L	160 mm
Thread depth	67.5 mm
Thread type	M
Thread size	M27×1.25
Coating	TiN
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap