

**Garant**
**Spiral flute machine tap, TiN, MF: M45X4**

**Order data**

Order number	130015 M45X4
GTIN	4062406021368
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 4 mm

Overall length L: 220 mm

Shank  $\varnothing$  D<sub>s</sub>: 36 mm

Shank square □: 29 mm

Tapping hole  $\varnothing$ : 41 mm

**Technical description**

Thread pitch	4 mm
Thread $\varnothing$	45 mm
Tapping hole $\varnothing$	41 mm
Overall length L	220 mm
Standard	DIN 376
Thread depth	112.5 mm

Number of clamping slots	4
Tool material	HSS E
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Shank $\varnothing D_s$	36 mm
Shank square $\square$	29 mm
Number of cutting edges Z	4
Thread type	M
Thread size	M45x4
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap