

**Garant**
**Spiral flute machine tap, TiN, MF: M38X3**

**Order data**

Order number	130015 M38X3
GTIN	4062406020958
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 3 mm

Overall length L: 200 mm

Shank  $\varnothing$  D<sub>s</sub>: 32 mm

Shank square □: 24 mm

Tapping hole  $\varnothing$ : 35 mm

**Technical description**

Thread $\varnothing$	38 mm
Thread depth	95 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX

Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread pitch	3 mm
Number of clamping slots	4
Standard	DIN 376
Shank square □	24 mm
Tapping hole Ø	35 mm
Overall length L	200 mm
Number of cutting edges Z	4
Shank Ø D <sub>s</sub>	32 mm
Tool material	HSS E
Thread type	M
Thread size	M38×3
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap