

Garant
Left-hand thread through hole and blind hole machine tap, uncoated, MF: M62X0,75

Order data

Order number	130021 M62X0,75
GTIN	4062406027940
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: MF-LH
 Tool material: HSS
 Standard: DIN 2184
 Tolerance class: ISO 1 4H
 Tolerance class: ISO 1X 4HX
 Tolerance class: ISO 2 6H
 Thread pitch: 0.75 mm
 Overall length L: 160 mm
 Shank \varnothing D_s: 50 mm
 Shank square \square : 39 mm
 Tapping hole \varnothing : 61.25 mm

Technical description

Thread \varnothing	62 mm
Number of cutting edges Z	6
Number of clamping slots	6
Tapping hole \varnothing	61.25 mm
Tolerance class	ISO 1 4H

Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.05
Tolerance class	6H +0.10
Thread pitch	0.75 mm
Overall length L	160 mm
Tool material	HSS
Standard	DIN 2184
Shank square □	39 mm
Thread depth	93 mm
Shank $\varnothing D_s$	50 mm
Thread type	MF-LH
Thread size	M62×0.75
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Application for type of drilling	up to 1.5×D for blind holes

Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap