

**Garant**
**Left-hand thread blind hole machine tap, TiN, MF: M3,5X0,5**

**Order data**

Order number	130016 M3,5X0,5
GTIN	4062406022013
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days  
 Minimum order quantity: 3 pcs.  
 Special / custom-made product - return not possible  
 Thread type: MF-LH  
 Tool material: HSS E  
 Standard: DIN 371  
 Tolerance class: ISO 1 4H  
 Tolerance class: ISO 1X 4HX  
 Tolerance class: ISO 2 6H  
 Thread pitch: 0.5 mm  
 Overall length L: 56 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 4 mm  
 Shank square  $\square$ : 3 mm  
 Tapping hole  $\varnothing$ : 3 mm

**Technical description**

Tapping hole $\varnothing$	3 mm
Number of cutting edges Z	3
Standard	DIN 371
Shank square $\square$	3 mm
Thread depth	8.75 mm
Tolerance class	ISO 1 4H

Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tool material	HSS E
Overall length L	56 mm
Number of clamping slots	3
Thread Ø	3.5 mm
Shank Ø D <sub>s</sub>	4 mm
Thread pitch	0.5 mm
Thread type	MF-LH
Thread size	M3.5×0.5
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap