

Garant**Left-hand thread blind hole machine tap, TiN, MF: M12X0,5****Order data**

Order number	130016 M12X0,5
GTIN	4062406022440
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 110 mm

Shank Ø D_s: 9 mm

Shank square □: 7 mm

Tapping hole Ø: 11.5 mm

Technical description

Tool material	HSS E
Number of clamping slots	3
Thread depth	30 mm
Shank Ø D _s	9 mm
Standard	DIN 376
Number of cutting edges Z	3

Overall length L	110 mm
Thread pitch	0.5 mm
Tapping hole Ø	11.5 mm
Shank square □	7 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread Ø	12 mm
Thread type	MF-LH
Thread size	M12×0.5
Coating	TiN
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring

without

Type of product

Tap