

**Garant**
**Machine tap for through holes and blind holes, TiN, MF: M58X0,5**

**Order data**

Order number	130025 M58X0,5
GTIN	4062406029968
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS

Standard: DIN 2184

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 160 mm

Shank  $\varnothing$  D<sub>s</sub>: 45 mm

Shank square □: 35 mm

Tapping hole  $\varnothing$ : 57.5 mm

**Technical description**

Thread $\varnothing$	58 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.20

Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.05
Tolerance class	6H +0.10
Thread pitch	0.5 mm
Number of cutting edges Z	6
Shank $\varnothing D_s$	45 mm
Tool material	HSS
Number of clamping slots	6
Tapping hole $\varnothing$	57.5 mm
Overall length L	160 mm
Shank square $\square$	35 mm
Standard	DIN 2184
Thread depth	87 mm
Thread type	M
Thread size	M58×0.5
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Application for type of drilling	up to 1.5×D for blind holes
Cutting direction	right-hand

Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap