

**Garant**
**Through hole machine tap, uncoated, Type: 1-8**

**Order data**

Order number	130030 1-8
GTIN	4062406035440
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: UNC  
 Tool material: HSS E  
 Standard: DIN 376  
 Threads per inch: 8  
 Thread  $\varnothing$ : 25.4 mm  
 Overall length L: 160 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 20 mm  
 Shank square  $\square$ : 16 mm  
 Tapping hole  $\varnothing$ : 22.15 mm

**Technical description**

Shank square $\square$	16 mm
Number of cutting edges Z	4
Tool material	HSS E
Thread $\varnothing$	25.4 mm
Number of clamping slots	4
Thread depth	76.2 mm
Thread pitch	3.175 mm

Shank $\varnothing D_s$	20 mm
Overall length L	160 mm
Tapping hole $\varnothing$	22.15 mm
Threads per inch	8
Standard	DIN 376
Thread type	UNC
Thread size	1-8 UNC
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap