

Garant
Through hole machine tap, uncoated, Type: NO.4-40

Order data

Order number	130030 NO.4-40
GTIN	4062406034313
Item class	10N

Description
Note:

Delivery time: 91 calendar days

Minimum order quantity: 25 pcs.

Special / custom-made product - return not possible

Thread type: UNC

Tool material: HSS E

Standard: DIN 371

Threads per inch: 40

Thread \varnothing : 2.85 mm

Overall length L: 56 mm

Shank \varnothing D_s: 3.5 mm

Shank square \square : 2.7 mm

Tapping hole \varnothing : 2.27 mm

Technical description

Overall length L	56 mm
Number of cutting edges Z	3
Thread \varnothing	2.85 mm
Number of clamping slots	3
Tapping hole \varnothing	2.27 mm
Tool material	HSS E
Shank square \square	2.7 mm

Standard	DIN 371
Thread depth	8.55 mm
Thread pitch	0.635 mm
Shank $\varnothing D_s$	3.5 mm
Threads per inch	40
Thread type	UNC
Thread size	4-40 UNC
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap